



# Q3 - Clinic kick-off promotion

Promotion runs strictly July 1<sup>st</sup> – September 30<sup>th</sup> 2026

## lara



**Lara 22L Ref: 19942122**

Start strong with **10% off** Lara's trusted Type B sterilisation in ~38 minutes!



**PROMO PRICE:**

**\$ 14,355.00 GST incl.**

**“Leap ahead with Lara”**

## U-son



**U-Son 3L Ref: 19600004**

**U-Son 6L Ref: 19600005**

Get ahead from the first step with **15% off** U-Son! Plus get a **free** BePro Soaking bath valued at \$124.28!



**U-Son 3L  
PROMO  
PRICE:**

**\$1,404.14  
GST incl.**

**U-Son 6L  
PROMO  
PRICE:**

**\$2,136.74  
GST incl.**

**“Get one up with U-Son”**

# Q3 - Clinic kick-off promotion!



Promotion runs strictly July 1<sup>st</sup> – September 30<sup>th</sup> 2026



implantmed<sup>PLUS</sup>

**Implantmed Plus Set 3**

**Ref: 90000163**

Take **15% off** Implantmed Plus Set 3 to enter Oral Surgery and Implantology with impact!

PROMO PRICE!

**\$6,965.75 GST incl.**

**“Make an impact with Implantmed”**

## “Always Performing with Alegra”



**Alegra HE-43 Straight Handpiece - Ref: 30119000**

Head Size: Ø 10.1mm  
Gear Ratio: 1:1 (Blue Band)  
Chuck: Twist Chuck  
Spray (optional): Single External  
Connection: ISO:3964 E-Type



alegra

PROMO PRICE!

**\$376.25 GST incl.**



**Alegra WE-56 Contra-Angle - Ref: 30116000**

Head Size: Ø 10.1mm  
Gear Ratio: 1:1 (Blue Band)  
Chuck: Push Button  
Spray (optional): Single external  
Connection: ISO:3964 E-Type



alegra

PROMO PRICE!

**\$514.25 GST incl.**



**Alegra TE-97 Turbine - Ref: 30068000**

Head size: Ø10.4mm  
Power\*: 16W  
Spray: Triple  
Coupling: RotoQuick RQ-03, RQ-04 & RQ-14



alegra

PROMO PRICE!

**\$729.95 GST incl.**



**Alegra TE-98 Turbine - Ref: 30071000**

Head size: Ø12.2mm  
Power\*: 18W  
Spray: Triple  
Coupling: RotoQuick RQ-03, RQ-04 & RQ-14



alegra

PROMO PRICE!

**\$921.27 GST incl.**

\* Performance value applies at a rated pressure of 2.5 bar for turbines without light, of 2.8 bar for turbines with light and exhaust air pressure of max. 0.2 bar. When operating with the maximum permissible operating pressure of 2.8 bar, it is possible to reach 16 watt for TE-97 and 18 watt for TE-98